

Utility Dipper

Simple Liquid Sampler


An all stainless steel sampler suitable for sampling liquids and suspensions.

- Takes a sample at the surface of the liquid
- Made from 304 Stainless steel

Operation

1. Insert the sampler into the product. The liquid will flow into the sampler.
2. Withdraw the sampler from the product
3. Raise the centre control rod to discharge the sample

Liquid Samplers



Raise the centre control rod (shown in red) to discharge the product



Stock No.	Length	Volume	Cup Diameter
675 5170A50	460mm	50ml	32mm
675 5170A100	540mm	100ml	32mm

[QUICK QUOTE LINK](#)

[ONLINE PRICING LINK](#)